



Rollmatic APS 002
DIMENSIONI SUGGERITE PER SACCHETTO
SUGGESTED BAG DIMENSIONS




Rollmatic APS002


1




2




3




4




5




6



7




8



Rollmatic APS002

montaggio base / base assembly



Ref.	Descriz. componente	Component	Q.ty
1	Ripiano Base Supporto	Shelf	1
2	Gamba Base	Legs	4
3	Piastra filettata	Corner Reinforcement	4
4	Piedino reg. M16 x 130	Adjustable Foot M16 x 130	4
5	Rosetta -Uni 6592-TE- ø16	Washer UNI 6592 - TE - ø16	8
6	Dado es. basso-Uni 5589-M16	Nut UNI 5589 - M16	8
7	Rosetta -Uni 6592-TE- ø6	Washer UNI 6592 - TE - ø6	16
8	Viti a bottone El -Uni-Iso 7380-M6x10	Screw El - UNI-ISO 7380 - M6x10	16

230V 50/60 HZ
MONOFASE

